

Obesity scale KERN MPT



APPROVED MEDICAL DEVICE





Compact personal floor scale with obesity range with EC type approval class III and approval for professional mobile or stationary medical use in medical diagnostics

Features

- · Verification class III (verification is optional)
- · Approved as a medical device according to 93/42/EEC
- · Ideally suited for hospitals, clinics and doctor's surgeries as well as for mobile applications such as home visits or at sports events
- · Thanks to the wide weighing range from 0 to 300 kg, this scale can be used to weigh children, adults of normal weight and overweight persons
- · Large platform with non-slip and wearresistant surface made of plastic, to provide a secure footing for patients
- · Secure and non-slip positioning with height-adjustable rubber feet
- · Level indicator to level the balance precisely
- · Robust and compact design
- · Hold function:

When patients do not stand completely still, a stable weight is calculated using an average weight and this is then "frozen". This means that you have sufficient time to attend to the patient first and then take the weight reading in peace

- · BMI function to determine underweight/ normal weight/surplus weight
- · Wall mount for the display device
- · Sturdy handle for easy transportation of
- · Battery- or mains-powered, rechargeable battery operation optional
- · Protective working cover included with delivery

Technical data

- · LCD display, digit height 25 mm
- · Dimensions of weighing plate W×D×H 450×340×90 mm
- · Dimensions of display device W×D×H 210×110×50 mm
- Cable length of display device approx. 150 cm
- Battery operation possible, 6×1,5 V AA, not included, operating time up to 57 h
- · Mains adapter external, standard
- Net weight approx. 8,5 kg

Accessories

- 11 Stand to elevate display device, height of stand approx. 950 mm, KERN MWS-A01
- · 2 Mechanical height rod, measuring range between 60-205 cm, for wall-mounting, approved as a medical device according to 93/42/EEC, KERN MSF 200
- · Protective working cover over the display device, scope of delivery: 5 items, KERN EOB-A02S05
- · Cleaning cloths, alcohol-free cloths for wipe disinfectant. Fulfill the legal requirements for occupational safety in accordance with TRGS 525/540. Packaging contents 80 pcs., size 20×22 cm per cloth, KERN MYC-01
- · Internal rechargeable battery pack, operating time up to 50 h, charging time approx. 24 h, KERN FOB-A08
- · Interface cable RS-232C to connect an external device, KERN MPS-A08
- Matrix needle printer, KERN YKN-01
- Label printer, KERN YKE-01
- Thermal printer, KERN YKB-01N
- · Further details, plenty of further accessories and suitable printers see Internet

STANDARD OPTION RS 232 MOVE BATT





* Within the EU, official verification is mandatory by law for scales that are intended for use as a medical device. Please add this to your order. We require the location of use and the post code for the verification.

Model	Weighing range	Readability	Verification value	Mandatory by law Verification
	[Max]	[d]	[e]	MIII
KERN	kg	kg	kg	KERN
MPT 300K100M	300	0,1	0,1	965-129



Pictograms



Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required.



Memory:

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



Data interface RS-232:

To connect the balance to a printer, PC or network



RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



KERN Communication Protocol (KCP):

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



Bluetooth* data interface:

To transfer data from the balance to a printer, PC or other peripherals



Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



Statistics:

using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software:

to transfer the measurements from the device to a PC



GLP/ISO-Protokoll:

With date and time. Only with KERN printers



Piece counting:

Reference quantities selectable. Display can be switched from piece to weight



Totalising level A:

The weights of similar items can be added together and the total can be printed out.



Weighing units:

Can be switched to e.g. nonmetric units at the touch of a key. Please refer to website for more details



Weighing with tolerance range:

(Check weighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model





ZERO:

Resets the display to "0"



Hold function:

When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight



Hold function:

When the weighing conditions are unstable, a stable weight is calculated as an average



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram.



Stainless steel:

The balance is protected against corrosion.



Suspended weighing:

Load support with hook on the underside of the balance.



Battery operation:

Ready for battery operation. The battery type is specified for each device.



Rechargeable battery pack:

Rechargeable set.



Battery operation rechargable:

Prepared for a rechargable battery operation



Universal mains adapter:

with universal input and optional input socket adapters for A) EU, CH B) EU, CH, GB, USA



Mains adapter:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available.



Power supply:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Weighing principle: Strain gauges

Electrical resistor on an elastic deforming body.



Peak hold function:

capturing a peak value within a measuring process.



Push and Pull:

the measuring device can capture tension and compression forces.



Integrated scale:

In the eyepiece.



360° rotatable microscope head



Monocular Microscope:

For the inspection with one eye.



Binocular Microscope:

For the inspection with both eyes



Trinocular Microscope:

For the inspection with both eyes and the additional option for the connection of a



Abbe Condenser:

With high numerical aperture for the concentration and the focusing of light.



Halogen illumination:

For pictures bright and rich in contrast.



LED illumination:

Cold, energy saving and especially long-life illumination.



Fluorescence illumination for compound microscopes:

With 100 W mercury lamp and filter.



Fluorescence illumination for compound microscopes:

With 3W LED illumination and filter.



Phase contrast unit:

For a higher contrast.



Darkfield condenser/unit:

For a higher contrast due to indirect illumination



Polarising unit:

To polarise the light.



Infinity system:

Infinity corrected optical system.



Automatic temperature compesation:

For measurements between 10 °C and 30 °C



Verification possible:

The time required for verification is specified in the pictogram.



Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram.



Pallet shipment:

The time required for internal shipping preparations is shown in days in the

The Bluetooth word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.